



designed for scientists



T 10 battery Complete Solution

/// Data Sheet

The T 10 battery Complete Solution provides a complete solution for benchtop dispersing operation and includes a reusable stainless steel dispersing tool (5 mm), a stand and a clamp in the scope of delivery.

Features:

- Large LCD display allows for easy parameter viewing
- Brushless DC motor for quieter operation
- Precise speed setting with numerical values
- Timer and counter functions for reproducible and precise operation



designed for scientists

- Rechargeable battery with two charging options: Either directly through a USB-C cable or via a charging clamp
- Labworldsoft compatible for remote control and data export and documentation

Scope of delivery

- T 10 battery ULTRA-TURRAX®
- S 10 N - 5 G Dispersing tool
- H 44 Boss head clamp
- R 104 Stand



designed for scientists

Technical Data

Motor rating input [W]	30
Motor rating output [W]	25
Volume range (H ₂ O) [l]	0.0005 - 0.1
Viscosity max. [mPas]	200
Speed range [rpm]	8000 - 30000
Speed deviation [%]	5
Speed adjustment	stepless
Speed display	LCD
Noise without element [dB(A)]	65
Motor principle	Brushless DC
Process type	batch
Power-ON time [min]	10
Power-OFF time [min]	5
Timer	yes
Timer display	LCD
Dimensions (W x H x D) [mm]	53 x 239 x 70
Weight [kg]	0.5
Permissible ambient temperature [°C]	5 - 40
Permissible relative humidity [%]	80
USB interface	USB-C
Power input max. [W]	45
Power input standby [W]	0.1
DC Voltage [V=]	15
Current consumption [mA]	3000